



Nashers and Sanitizers to Automatically Wash and Apply Disinfectant to Wheelchairs and Other Hard-to-Clean Medical Equipment.

Designed for Durable & Home Medical Equipment

A larger chamber, more spray arms & increased pressure. A multi-purpose system with a small footprint - an Aqua Phase Workhorse

STANDARD FEATURES -

Structural

- Double Wall Stainless Steel Chamber
- Stainless Steel Structural Frame
- Stainless Steel Control Enclosure
- Oscillating Stainless Steel Spray Arms
- Chamber Floor Deck & Loading ramps
 Automatic Chemical Injection
- Caster Wheels & Leveling Feet
- Seal Welded Wash Chamber
- Front Door 12ga Stainless Steel
- Front Door Safety Window
- Disinfectant Application System
- Fill Line Temperature Gauge 3" Dial

Controls & Electrical

- Programmable Logic Control Syst (PLC) Wash PSI: 32
- 24 Volt DC Control System
- LCD Status Display
- Level Control Self Diagnostics
- Wash Cycle Pressure Monitoring
- Non-Reset Cycle Counter
- GFCI Built in Circuit
- 230 Volt, 25 Amp, 50/60 Hertz SP

Cycles

- Variable Time Cycles (3, 5, or 7 min)
- Run Mode & Drain Mode Selection
- 'Clean Only', 'Clean & Apply Disinfectant' and 'Apply Disinfectant Only' cycles
- Automatic Filling & Draining

Mechanical

• 3 HP Motor/Stainless Steel Pump

Wash System Nozzle Data

- Wash & Rinse System Nozzles: 35
- Disinfectant Nozzles: 16
- Capacity Gallons/min: 52.5
- Capacity Gallons/cycle: 367.5
- Capacity Gallons/hour: 3150

Extras

- Fill & Drain Hose Set 10' Each
 - Fire Equipment/KEDS Wash Rack Stainless SteelDisinfectant
 - Application Spray Wand (Exterior Mounted)
 - Wash-Down Spray Gun & Hose (Exterior Mounted)
 - Back Flow Prevention Devices / System
 - Water Supply Temperature Mixing Valve (1/2" or 3/4" Line Size)
 - Disinfectant Mixing Station (Exterior Mounted)
 - Air Dry Blower

OPTIONAL FEATURES & UPGRADES • Lighted Wash Chamber

- Utility Wash Tray Set Stainless Steel
- Digital Temperature Display
- Pass-Through Design (Entry/Exit Doors)
- Conveyor Belt Transfer System
- Data Collections Computer System
- Loading Ramp Set (2 @ 48"L x 16"W)

DIMENSIONS & WEIGHT -

Exterior • Length: 59-13/16"

• Width: 65"

• Height: 73"

- Length: 55-1/2"
 - Width: 40-1/4"
 - Height: 46-5/8"
- Crate/Pallet Dimensions
 - Length: 80"
 - Width: 60"
 - Height: 84"

Approximate Shipping Weight

V131201

- 1750 lbs.
- 794 Kilo

Once the Aqua Phase unit is in its location, all you need to do is hook up two hoses - one for the hot water fill line and one for the drain line. Then plug the Aqua Phase in an appropriate power source & begin saving time, improving efficiency & enhancing your infection control protocol.

> Aqua Phase, A Division of Mid-State Stainless, Inc. / 330 W. Benson Ave. / PO Box 228 / Grantsburg, WI 54840 / USA p: 800-208-9274 | f: 715-463-5853 | aquaphase@medwashers.com | www.aqua-phase.com



