

AQ-F250 Features & Options

Washers and Sanitizers to Automatically Wash and Apply Disinfectant to Wheelchairs and Other Hard-to-Clean Medical Equipment.

BASIC WASHER

Compare features, options, and pricing of our Basic Washer - AQ-F250 Add the Disinfectant Application System and your infection control protocols can be met. This model is functional for smaller nursing homes.

STANDARD FEATURES -

Structural

- Double Wall Stainless Steel Chamber
- Stainless Steel Structural Frame
- Stainless Steel Control Panel Enclosure
- PVC Stationary Spray Arms 1" Pipe
- Chamber Floor Deck
- Caster Wheels (2,400lb rating)
- Seal Welded Wash Chamber
- Front Door 12ga Stainless Steel

Controls & Electrical

- Programmable Logic Control Syst (PLC)
- 24 Volt DC Control System
- LCD Status Display
- Level Control Self Diagnostics
- Power Cord with GFCI Built in Circuit
- 115 Volt, 20 Amp, 60 Hertz System

Cycles

- Variable Time Cycles (3, 5, or 7 min)
- Run Mode & Drain Mode Selection
- Clean & Rinse Wash Cycles
- Automatic Chemical Injection
- Automatic Filling & Draining

Mechanical

• 1 HP Motor / Stainless Steel Pump

Wash System Nozzle Data

- 24 Wash & Rinse System Nozzles
- Wash PSI: 24
- Capacity Gallons/min: 36
- Capacity Gallons/cycle: 252
- Capacity Gallons/hour: 2160

Extras

• Fill & Drain Hose Set - 10' Each



OPTIONAL FEATURES & UPGRADES -

- Disinfectant Application System
- Front Door Safety Window
- Lighted Wash Chamber
- Utility Wash Tray Set Stainless Steel
- Digital Temperature Display
- Non-Reset Cycle Counter
- Wash Cycle Pressure Monitoring
- Loading Ramps
- Disinfectant Application Spray Wand (Exterior Mounted)

- Wash-Down Spray Gun & Hose (Exterior Mounted)
- Back Flow Prevention Devices / System
- Water Supply Temperature Mixing Valve (1/2" or 3/4" Line Size)
- Disinfectant Mixing Station (Exterior Mounted)
- Fill Line Water Temperature Gauge 3" Dial
- Specialized Cycle Sequencing

DIMENSIONS & WEIGHT-

Exterior

- Length: 68-1/6"
- Width: 34"
- Height: 61-3/8"

Chamber with Floor Deck

- Length: 48-3/8"
- Width: 27-1/4"
- Height: 39-3/16"

Crate/Pallet Dimensions

- Length: 71"
- Width: 39"
- Height: 74"

Approximate Shipping

Weight

- 700 lbs.
- 317 Kilo

Once the Aqua Phase unit is in its location, all you need to do is hook up two hoses - one for the hot water fill line and one for the drain line. Then plug the Aqua Phase in an appropriate power source & begin saving time, improving efficiency & enhancing your infection control protocol.