

# AQ-1270 Features & Options

Nashers and Sanitizers to Automatically Wash and Apply Disinfectant to Wheelchairs and Other Hard-to-Clean Medical Equipment.

# STRETCHED VERSION OF THE AQ-1000

Taller & Longer than the AQ-1000 - see below for dimensions

### STANDARD FEATURES

#### Structural

- Double Wall Stainless Steel Chamber
- Stainless Steel Structural Frame
- Stainless Steel Control Enclosure
- Stationary Stainless Steel Spray Arms
- Chamber Floor Deck
- Caster Wheels (2,400lb rating)
- Seal Welded Wash Chamber
- Front Door 12ga Stainless Steel

#### Controls & Electrical

- Programmable Logic Control Syst (PLC)
- 24 Volt DC Control System
- LCD Status Display
- Level Control Self Diagnostics
- Power Cord with GFCI Built in Circuit
- 115 Volt, 20 Amp, 60 Hertz System
- UL, CSA, CE/EU

#### Cycles

- Variable Time Cycles (3, 5, or 7 min)
- Run Mode & Drain Mode Selection
- Clean & Rinse Wash Cycles
- Automatic Chemical Injection
- Automatic Filling & Draining

# Mechanical

• 1 HP Motor / Stainless Steel Pump

#### Wash System Nozzle Data

- Wash & Rinse System Nozzles: 23
- Wash PSI: 22
- Capacity Gallons/min: 37.5
- Capacity Gallons/cycle: 262.5
- Capacity Gallons/hour: 2250

#### Extras

• Fill & Drain Hose Set - 10' Each



# OPTIONAL FEATURES & UPGRADES -

- Disinfectant Application System
- Front Door Safety Window
- Lighted Wash Chamber
- Utility Wash Tray Set Stainless Steel
- Equipment Rack SS HME/DME
- Wheelchair Wheel Rotation System
- Digital Temperature Display
- Non-Reset Cycle Counter
- Wash Cycle Pressure Monitoring
- Loading Ramps

- Disinfectant Application Spray Wand (Exterior Mounted)
- Wash-Down Spray Gun & Hose (Exterior Mounted)
- Back Flow Prevention Devices / System
- Water Supply Temperature Mixing Valve (1/2" or 3/4" Line Size)
- Disinfectant Mixing Station (Exterior Mounted)
- Fill Line Water Temperature Gauge 3" Dial
- 1-1/2HP Motor / Stainless Steel Pump
- 208/230v, 25Amp, 50/60Hz, Single Phase Operation
- Specialized Cycle Sequencing
- Air Dry Blower

# **DIMENSIONS & WEIGHT-**

#### Exterior

- Length: 74-11/16"
- Width: 34"
- Height: 72-3/8"

#### Chamber with Floor Deck

- Length: 56-1/2"
- Width: 25-3/4"
- Height: 48-1/2"

#### Crate/Pallet Dimensions

- Length: 80"
- Width: 39"
- Heiaht: 84"

# Approximate Shipping

#### Weight

- 925 lbs.
- 419 Kilo

Once the Aqua Phase unit is in its location, all you need to do is hook up two hoses - one for the hot water fill line and one for the drain line. Then plug the Aqua Phase in an appropriate power source & begin saving time, improving efficiency & enhancing your infection control protocol.