

AQ-3000 Features & Options

Nashers and Sanitizers to Automatically Wash and Apply Disinfectant to Wheelchairs and Other Hard-to-Clean Medical Equipment.

DISINFECTANT APPLICATION SYSTEM STANDARD

This model is the "Work Horse" of the Aqua Phase Classic Series

STANDARD FEATURES -

Structural

- Double Wall Stainless Steel Chamber
- Stainless Steel Structural Frame
- Stainless Steel Control Enclosure
- Oscillating Stainless Steel Spray Arms
- Caster Wheels (2,400lb rating)
- Seal Welded Wash Chamber
- Front Door 12ga Stainless Steel
- Wheelchair Wheel Rotation System
- Front Door Safety Window
- Disinfectant Application System

Controls & Electrical

- Programmable Logic Control Syst (PLC)
- 24 Volt DC Control System
- LCD Status Display
- Level Control Self Diagnostics
- Wash Cycle Pressure Monitoring
- Non-Reset Cycle Counter
- Power Cord with GFCI Built in Circuit
- 115 Volt, 30 Amp, 60 Hertz System
- UL, CSA, CE/EU

Cycles

- Variable Time Cycles (3, 5, or 7 min)
- Run Mode & Drain Mode Selection
- Clean Only, Clean & Apply Disinfectant, and Apply Disinfectant Only modes
- Automatic Chemical Injection
- Automatic Filling & Draining

Mechanical

- 1-1/2 HP Motor/Stainless Steel Pump
- Wheelchair Loading Carriage Assm

Wash System Nozzle Data

- Wash & Rinse System Nozzles: 23
- Disinfectant Nozzles: 7
- Wash PSI: 36
- Capacity Gallons/min: 37.5
- Capacity Gallons/cycle: 262.5
- Capacity Gallons/hour: 2250

- Fill & Drain Hose Set 10' Each
- Loading Ramp Set (2 @ 32"L x 6"W)



Shown with optional Mixing Station & Disinfectant Application Wand

OPTIONAL FEATURES & UPGRADES -

- Lighted Wash Chamber
- Utility Wash Tray Set Stainless Steel
- Equipment Wash Rack SS HME/DME
- Digital Temperature Display
- Pass-Through Design (Entry/Exit Doors)
- Data Collections Computer System
- Disinfectant Application Spray Wand (Exterior Mounted)
- Wash-Down Spray Gun & Hose (Exterior Mounted)

- Back Flow Prevention Devices / System
- Water Supply Temperature Mixing Valve (1/2" or 3/4" Line Size)
- Disinfectant Mixing Station (Exterior Mounted)
- Fill Line Water Temperature Gauge 3" Dial
- 3HP Motor / Stainless Steel Pump
- 208/230v, 25Amp, 50/60Hz, Single Phase Operation
- Specialized Cycle Sequencing
- Air Dry Blower

DIMENSIONS & WEIGHT -

Exterior

- Length: 68-1/16"
- Width: 34"
- Height: 61-5/8"

Chamber w/ Wheel Rotation System

- Length: 50-1/4"
 - Width: 25-3/4"
 - Height: 34-3/4"

- Length: 71"
- Width: 39"
- Height: 74"

Crate/Pallet Dimensions Approximate Shipping

Weight

- 990 lbs.
- 4341 Kilo

Once the Aqua Phase unit is in its location, all you need to do is hook up two hoses - one for the hot water fill line and one for the drain line. Then plug the Aqua Phase in an appropriate power source & begin saving time, improving efficiency & enhancing your infection control protocol.