

AQ-4800 Features & Options

Nashers and Sanitizers to Automatically Wash and Apply Disinfectant to Wheelchairs and Other Hard-to-Clean Medical Equipment.

BARIATRIC WIDTH WASH CHAMBER

AQ-4800 is one of the widest Aqua Phase models available

STANDARD FEATURES

Structural

- Double Wall Stainless Steel Chamber
- Stainless Steel Structural Frame
- Stainless Steel Control Panel Enclosure
- Oscillating Stainless Steel Spray Arms
- Chamber Floor Deck & Loading ramps
- Caster Wheels & Leveling Feet
- Seal Welded Wash Chamber
- Front Door 12ga Stainless Steel
- Front Door Safety Window
- Disinfectant Application System
- Lighted Wash Chamber
- Fill Line Temperature Gauge 3" Dial

Controls & Electrical

- Programmable Logic Control Syst (PLC)
- 24 Volt DC Control System
- LCD Status Display
- Level Control Self Diagnostics
- Wash Cycle Pressure Monitoring
- Non-Reset Cycle Counter
- GFCI Built in Circuit
- 208/230 Volt, 40 Amp, 50/60 Hertz SP
- UL, CSA, CE/EU

Cycles

- Variable Time Cycles (3, 5, or 7 min)
- Run Mode & Drain Mode Selection
- Clean Only, Clean & Apply Disinfectant, and Apply Disinfectant Only modes
- Automatic Chemical Injection
- Automatic Filling & Draining

Mechanical

• 3 HP Motor/Stainless Steel Pump

Wash System Nozzle Data

- Wash & Rinse System Nozzles: 83
- Disinfectant Nozzles: 36
- Wash PSI: 30
- Capacity Gallons/min: 113
- Capacity Gallons/cycle: 791
- Capacity Gallons/hour: 6780

Extras

- Fill & Drain Hose Set 10' Each
- Loading Ramp Set (2 @ 48"L x 16"W)
- Indicate Door Swing(s) to fit your location



OPTIONAL FEATURES & UPGRADES

- Digital Temperature Display
- Pass-Through Design (Entry/Exit Doors)
- Conveyor Belt Transfer System
- Data Collections Computer System
- Fire Equipment/KEDS Wash Rack Stainless Steel
- Chamber Swing Arms to wash Backboards

- Disinfectant Application Spray Wand (Exterior Mounted)
- Wash-Down Spray Gun & Hose (Exterior Mounted)
- Back Flow Prevention Devices / System
- Water Supply Temperature Mixing Valve (1/2" or 3/4" Line Size)
- Disinfectant Mixing Station (Exterior Mounted)
- Specialized Cycle Sequencing

DIMENSIONS & WEIGHT -

Exterior

- Length: 113-1/2"Width: 75-1/8"
- Height: 79"

Chamber with Floor Deck

- Length: 104-3/8"
- Width: 51"
- Height: 53-1/16"

Crate/Pallet Dimensions

- Length: 3 Pallets
- Width:
- Height:

Approximate Shipping

- Weight
 - 3400 lbs.
 - 1542 Kilo

Door Opening Requirements: Width: 55" x Height: 72-15/16"

Once the Aqua Phase unit is in its location, all you need to do is hook up two hoses - one for the hot water fill line and one for the drain line. Then plug the Aqua Phase in an appropriate power source & begin saving time, improving efficiency & enhancing your infection control protocol.